

Comparison between the M4D Scan and the Structure Sensor with Captevia App

M4D SCAN



STRUCTURE SENSOR + CAPTEVIA



Specifications		
Light source	White Light (LED)	Structured Light
Weight	850 g	450 g
Accuracy	Up to 0,5 mm	Around 4 mm
Stand-off distance	+/- 40 cm	+/- 60 cm
Connection Standard	USB 2.0	Wi-Fi
O&P Applications		
Plantar Surface	★★★★	★★★★★
AFO	★★★★	★★★★★
Knee	★★★★	★★★★★
Torso	★★★★	★★★★★
Prosthetics	★★★★	★★★★★
Seats	★★★★	★★★★★
Cranial	★★★★	★★★★★
Footwear	★★★★	-
Hand	★★★★	-